## **Aqualine Separator Filters**

The Aqualine separator filter system works using the principle of centrifugal force to drive heavier solid particles down to the bottom of the vessel to a collection area. The collected sediment is emptied periodically manually or using an automatic self cleaning device.

- ➢ Holds particles between 70 − 110 microns
- Works at high capacity
- Cleaning can be done during service
- No moving parts internally
- Made of SS304 Stainless and St-37 Carbon steel
- No pressure loss
- Operating pressure 8 Bar
- No risk of elements blocking

Aqualine SP Series Technical Table			<b>Connection Type</b>	Dimensions			Floor
Model	Capacity (m <sup>3</sup> /h)	Weight	Inlet / Outlet	Width	Length	Height	Standing
Aqualine SP 150	2 to 7.5	6.1	3/4" BSP Male	140	176	780	No
Aqualine SP 175	6.5 to 11	7.7	1" BSP Male	168	208	775	No
Aqualine SP 250 🦯	14.5 to 18	10	1-1/2" BSP Male	168	223	775	No
Aqualine SP 350	17 to 24.5	18.5	2" BSP Male	410	450	1185	Yes